

Immersion Thermostat with Plug & Play Technology. Powerful pressure and suction pump made of high-resistant plastic. Moistened parts in stainless steel or high-resistant plastics. With adjustable overtemperature protection according to DIN 12876.

Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

4-year warranty - registration required.

Technical data according to DIN 12876

Operating temperature range	25...200 °C	Order-No.: 2061.0001.01
with water cooling	20...200 °C	
with refrigerator	-30...200 °C	
Temperature stability at 70°C	0,01 K	
temperature set point / display	5,7" colour Touchscreen	
Absolute accuracy	setup for calibration	
Internal temperature sensor	Pt100	
Sensor external connection	Pt100	
Interface digital	Ethernet, USB (Host u. Device), RS232	
Safety classification	III / FL	
Heating power at 240V	2,1 kW	
Heating power at 230V	2 kW	
Heating power at 220V	1,8 kW	
Heating power at 208V	1,6 kW	
Heating power at 200V	1,5 kW	
Pressure pump	yes	
max. delivery	22 l/min	
max. delivery pressure	0,4 bar	
Suction pump	yes	
max. delivery (suction)	17 l/min	
max. delivery pressure (suction)	0,25 bar	
Pump connection (optional)	M16x1 male	
Immersion depth	195 mm	
Overall dimensions WxDxH **	132x159x360 mm	
Net weight	5 kg	
Power supply requirement	200-240V 1~/2~ 50/60Hz	
Power input	2,1 kW	
max. current	10 A	
min. Fuse	10A	
max. Fuse	16A	
Pressure equipment category	Art. 4.3 PED	
Degree of Protection	IP20	
min. ambient temperature	5 °C	
max. ambient temperature	40 °C	

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Accessories and periphery: mini-USB cable #54949*, screw clamp #30541*, cooling coil #39668, dummy plugs, sleeve nuts thread M16x1, pump adaptor #39593, Note: When using Huber pump adapter: Polyglycol is not permissible to be used as a heat transfer fluid, hose connector NW12 #6087, connection tubes, waterbaths in polycarbonat and stainless steel

* standard equipment

Output data valid for: Room temperature 20° C

In accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 10%, as long as the frequency tolerance does not run in the opposite direction.

Example: -10% voltage and + 3% frequency -> not allowed !

-10% voltage and -3% frequency -> allowed.

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
2. Three-phase devices with current consumption less than 63A --> with cable, without plug
3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

** Please respect space requirements. See operating conditions at www.huber-online.com