

**Technical data**

|                             |                                     |
|-----------------------------|-------------------------------------|
| Operating temperature range | -60...260 °C                        |
| Material                    | industrial plastic material<br>hose |
| Braiding                    | Yes                                 |
| Label*                      | Yes                                 |
| Nominal width (DN)          | 20 mm                               |
| Length                      | 200 cm                              |
| Net weight                  | 2,98 kg                             |
| Connection                  | M30x1,5                             |
| Outside diameter            | 44 mm                               |
| Max. pressure at 20°C       | 6 bar                               |
| Test pressure               | 1,25 bar                            |
| Min. bending radius         | 190 mm                              |
| Fire rating                 | UL94-HB                             |

**Order-No.: 9614****1.0/15**

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Insulation: Special insulation with silicon cover, ends secured and covered with silicon caps.

Note: Ball socket according to DIN 3863, sleeve nut according to DIN 3870.

\*Label: stamp on band: Order No., -60°C...260°C, PS 6 bar, KW/year